

# World-Class Equipment & Process Expertise

## **WDI-10 Elite Data Sheet**

## 10-GPM DEIONIZED WATER SYSTEM

System Feed		Flow Configuration	Alternating Duplex
Volume	Minimum 200 gallons	Regeneration	Countercurrent
SKID MOUNTED COMPONENTS		Waste Flow	2.7 gpm
Feed Pump		Cycle Time	50 minutes
Number	One (1)	Cation Exchangers	
Horsepower	2 HP	HCI per Cycle	1.5 gallons
Material	316 SS	Waste per cycle	80 gallons
Bag Filter		Grains Capacity	28,000
Number	One (1)	Anion Exchangers	
Filter Rating	5-micron	NaOH per cycle	1.3 gallons
Cation & Anion Exchangers		Waste per Cycle	89 gallons
Number	Two (2) of each	Grains Capacity	25,200
Vessel Size	10" x 40"	UTILITIES	
Construction	PE Lined Fiberglass	Electrical Voltage	208-230/460
Cation Resin	Strong Acid	Full Load Amps	10/5
Anion Resin	Strong Base	Make-up Water	10 gpm
Volume per Vessel	1.4 ft <sup>3</sup>	PHYSICAL DATA	
Controls		Footprint (LxWxH)	47" x 36" x 86"
Inlet Conductivity	Signet 2850	Shipping/Operating Wgt	850/900 lbs
Outlet Conductivity	Signet 2850	Frame/Coating	304SS/Polyurethane
Outlet Flow	Signet 2537	Piping	Schedule 80 PVC
Outlet pH	Signet 2750		
Controller	CompactLogix	1	

#### **OPERATING SPECIFICATIONS**

**Drum Low Level Sensors** 

Touchscreen

Feed Water Quality				
Temperature	40°F-110°F			
рН	3-10 SU			
TSS	<5 mg/L			
TDS	<450 mg/L			
Chlorine	<2 mg/L			
Product Water Quality				
TDS	<3 mg/L			
Conductivity	<5 (uS			
System Flow	10 gpm			

5.7" PanelView 7+ One (1) of Each





For more information visit www.waterinnovations.net

Contact at 760.294.1888 sales@waterinnovations.net



# World-Class Equipment & Process Expertise

# WDI-10 Elite Data Sheet 10-GPM DEIONIZED WATER SYSTEM

o-stage, separate bed ion exchange process. A water quality

Operating Profile Removes ions from tap water through a two-stage, separate bed ion exchange process. A water quality < 3 TDS will be achieved when the equipment is operated within parameters as listed. The deionizer shall provide a near continuous flow of deionized water through the use of a duplex (two tank) configuration. This duplex configuration shall operate with 50% of the resin in reserve or in regeneration. System regenerations shall be initiated by measuring the feed water quality and flow rate, to accumulate the total loading on the system. Once the accumulated load surpasses the system's operating capacity setpoint, a regeneration is initiated.

**System Pump** The system shall use a 2-HP multi-stage centrifugal pump to pressurize water to the proper operating pressures and flow for the deionizer. The pump is designed to draw water from an atmospheric source. A return loop is used to provide a continuous flow of water pass the pump during operation, preventing low flow conditions. Pump construction shall be 316 stainless steel.

Bag Filter - There is one (1) bag filter housing rated for 15-gpm flow with isolation valves allowing filter change-out. The housing is constructed of reinforced polypropylene with nominal 5 micron filter bags

Regeneration Valve One is used with each set of cation and anion vessels, providing service and regeneration control. Inlet and outlet ports accept a 3/4" quick connect, double O-ring sealed adapter made of PVC. The valve requires a minimum inlet operate pressure of 60 psi, to drive valve functions. The valve controls the counter-current regeneration process including acid draw opposite the service flow and rinsing employing a fixed-flow eductor

**Media Tank** The tanks shall measure 10" in diameter and 40" tall. A total of two each cation and anion tanks will be used with one tank of each in service at all times. Tanks made of fiberglass reinforced polyester with a 2.5" threaded top opening are designed for a maximum working pressure of 125 psi and hydrostatically tested at 300 psi. Tanks. The upper and lower distribution system shall be of a slot design providing even distribution of regeneration water.

**Deionization Media** Each Cation deionizer includes 1.4-ft³ per tank of 10% cross-linked high-capacity, strong acid resin with an exchange capacity of >20,000 grains/ft3 when regenerated with 4-lbs. of hydrochloric acid. Each anion deionizer also includes 1.4-ft³ of high-capacity weak & strong base anion resins with an exchange capacity of >18,000 grains/ft3 when regenerated with 6-lbs of NaOH. Inert plastic beads shall be used to pack the resin tanks, while still allowing the resin minimum space for expansion.

System Skid All system components are skid mounted and prewired. Installation hook-ups shall be limited to plumbing and electrical connections. Skid construction shall be from 304 grade stainless steel. Finish shall include cleaning and sandblasting. Skid dimensions shall not exceed 47" L x 36" W x 86" H. Skid design shall include anchoring feet for securing skid to foundation and grounding lugs for properly grounded electrical components.

System Controls – Operation, monitoring, and control of the integrated system utilizes an Allen-Bradley CompactLogix programmable automation controller (PAC) with Human-machine interface (HMI) through a Panelview Plus color touch screen. System operation while highly automated also employs manual control with an intuitive operator-friendly interface. Product water to process is assured with recirculation of "off-spec" water to the feed tank if above an operator-adjustable set point. System operating set points and alarms are set at the touch screen which is password protected to limit access to the operator, supervisor, maintenance, or engineer based on necessity and relative expertise.




For more information visit www.waterinnovations.net

Contact at 760.294.1888 sales@waterinnovations.net





## 10-GPM DEIONIZED WATER SYSTEM





For more information visit www.waterinnovations.net

Contact at 760.294.1888 sales@waterinnovations.net